

## TwinGuard ULT Freezers (-86°C)



MDF-DU302VX-PE (360L)

MDF-DU502VX-PE (528L)

MDF-DU702VX-PE (729L)

Extra sample security with Dual cooling system  
Maintain chamber temperature at -70°C  
even when one of the cooling systems is down

Color touch panel with datalogging function



## Sliding Door Laboratory Fridges

MPR-S150H-PE (165L)

MPR-S300H-PE (345L)

MPR-S500H-PE (554L)



>50% lower power consumption  
1.4 kWh/day<sup>1</sup>

Stable temperature uniformity  
±1°C at central test point<sup>1</sup>

Efficient cooling with  
Inverter technology + HC Refrigerant



<sup>1</sup> for 554 L model only